 <p>Not Actual Photo YIC International Co., Limited.</p>	<h2 style="color: red;">GMA301</h2>
	<p><b>Manufacturer Part Number:</b> GMA301</p> <p><b>Manufacturer/Brand:</b> MEMS</p> <p><b>Part of Description:</b> GMA301 MEMS</p> <p><b>RoHs Status:</b></p> <p><b>Stock Condition:</b> New original, 7010 pcs Stock Available.</p> <p><b>Ship From:</b> Hong Kong</p> <p><b>Shipment Way:</b> DHL/Fedex/TNT/UPS/EMS</p>
<p>Image may be representation. See specs for product details.</p>	









### Specifications

Part Number	GMA301
Manufacturer	MEMS
Description	GMA301 MEMS
Category	Integrated Circuits (ICs) > Specialized Hot ICs
Part Status	7010 pcs Stock
Series	-
RoHs Status	Lead free / RoHS Compliant
Condition	New Original Stock
Warranty	100% Perfect Functions
Lead Time	2-3days after payment.
Payment	PayPal / Telegraphic Transfer / Western Union
Shipping by	DHL / Fedex / UPS
Port	HongKong
RFQ Email	Info@Y-IC.com

GMA301 is New Original in Stock, Search GMA301 Datasheets, PDF, Inventory at Y-IC.com Online, Order GMA301 with warrantied and confidence. RFQ GMA301 : Info@Y-IC.com

### You May Be Also Be interested

In:

 <p><b>GMA300F-12-R3</b> Cosel AC/DC MEDICAL PS (OPEN FRAME; 30</p>	 <p><b>GMA30100HV</b> Sprague Goodman CAP TRIMMER</p>	 <p><b>GMA300F-24-J1</b> Cosel AC/DC MEDCAL PS (OPEN FRAME; 300</p>	 <p><b>GMA300F-24-R3</b> Cosel AC/DC MEDICAL PS (OPEN FRAME; 30</p>
 <p><b>GMA30300</b> Sprague Goodman CAP TRIM 16-100PF 175V THRU HOLE</p>	 <p><b>GMA302</b> GEMS GMA302 GEMS</p>	 <p><b>GMA30100</b> Sprague Goodman CAP TRIM 23.5-25PF 175V T/H</p>	 <p><b>GMA30200</b> Sprague Goodman CAP TRIM 7-40PF 175V THRU HOLE</p>

### Hot Parts

More

- |                         |                      |                     |                    |                       |
|-------------------------|----------------------|---------------------|--------------------|-----------------------|
| ⚙️ 155P05-110           | ➡️ ADC0820CIWM       | ➡️ BKO-CA1010H19    | D BZX384B56-GS08   | ➡️ CAT8801STB-GT3     |
| ⊖ CC0201DRNPO8BN5R6     | ⚙️ CC0805KRX7R0BB182 | D CC1206BRNPO9BN1R8 | ➡️ CY2291SL-237T   | ➡️ DIM800FSM12-A      |
| ⚙️ DMP3120L             | ⊖ DS90CF386MTDX      | ⚙️ F931C226MBA      | ➡️ FZT1149ATA      | ➡️ GRM0335C1HR30BA01J |
| D H52014FB              | ⚙️ IRFZ10PBF         | ⊖ IXTP02N120P       | ⚙️ KA78M06RTF      | ➡️ KD2319SRG          |
| ➡️ LM431BIMX            | ➡️ LT1372IS8#TRPBF   | ⚙️ LT3023IDD#PBF    | ⊖ LT3469ETS8#TRPBF | ➡️ M1583VC450         |
| ➡️ M4A3-64/32-10VC-12VI | ➡️ MA3036-H          | D MAX873AESA        | ⚙️ MCP6291T-E/OT   | ⊖ MT88L89CS           |
| ⚙️ NC7SZ38P5X           | D PD3R1600-7         | ➡️ PE60QL03N        | ➡️ PH300F280-2     | ➡️ PIC16F690T-I/SO    |
| ⊖ PMBT5401              | ⚙️ PS21204-B         | ➡️ PTH04050AAZ      | ➡️ PZM22NB1        | ➡️ SI1305LT-T1-E3     |
| ⚙️ SI2176-B30-GMR       | ⊖ SN74CBT16212DGGR   | ⚙️ SP6659EK1-1.8/TR | D TC35484BF        | ➡️ THS4502IDGN        |
| ➡️ TLC352CP             | ⚙️ TLE6389-2GV       | ⊖ TLK110PTR         | ⚙️ VNQ5E050AKTR-E  | ➡️ ZXMN20B28KTC       |

Contact us: [Info@Y-IC.com](mailto:Info@Y-IC.com)

ADD: Unit A5-B5 No.509, 5/F Sing Win Factory Building, 15-17 Shing yip St, Kwun Tong, Kowloon, HongKong.

Copyright © 2019 YIC International Co., Limited